

IPL-15 Classic

- Pressure Feed Roller



The IPL-15 Classic is a development of the now famous IPG-24/HV series and utilises proven technology from both the reliable IP-6000 series and IPG-24/HV. Components are thoroughly blended by a static mixer mounted on the machine, a pneumatically operated

solvent pump makes cleaning easy and the same catalyst dosage technology that has made Aplicator synonymous with quality products over the decades is used.

IPL-15 Classic

- Pressure Feed Roller

OPERATION

Aplicator's IPL-15 Classic machine works with an air driven dual-acting piston pump both for the resin and the catalyst. Manufactured from stainless steel, the catalyst pump incorporates a pressure gauge and pressure relief valve and is synchronised with the resin pump shaft for precise delivery of catalyst.

Consequently, it is independent of variations in air supply or material viscosity.

Catalyst volumes are easily adjusted with a hand wheel, which changes the stroke length of the catalyst pump. The mixing ratios are continuously variable. Catalyst is pumped directly from the original container. Resin is usually pumped from a 200-litre drum, but can also be pumped from a 25-litre pail, a bulk container or a fixed storage tank.

Components are mixed internally in a static mixer before the material is pumped through a single hose to the roller handle. As there is no handling of resin or catalyst in open containers, the working environment will be cleaner and safer.

To facilitate degassing and function checks the machine is additionally equipped with a unique recirculation system for the catalyst and resin.

SPECIAL FEATURES

- Recirculation of resin and catalyst
- Pneumatic push button operated pump for solvent flushing
- Static mixer
- Accurate catalyst dosage
- All dynamic seals are self lubricating and of the highest quality for minimum maintenance
- Two wheeled trolley for full mobility

The machine showed on the overleaf might have extra equipment, modifications might have been made since the brochures were printed.

INTERNAL MIXING

Aplicator have used the method of internal mixing of resin and catalyst for many years, which has consistently proved to be the best method for obviating the problems that can occur with incomplete mixing.

FLUSHING

Cleaning the roller dispenser after use is easily carried out by using the built-in, pneumatically operated flushing pump. Pressing the flush button on the pump will automatically flush the static mixer, hose and handle without manual handling of hazardous solvents.

TECHNICAL DATA Air supply:

Air consumption: Capacity:

Max. working pressure: Pressure ratio: Mixing ratio:

Hose length: Total weight: 6 Bar (90 psi) 90 litres / litre output Up to 6 litres/min, depending on viscosity, hose length/ diameter and nozzle orifice

90 Bar (1350 psi) 15:1 Continuously variable between 0.8 and 4.0 %

Standard length 10 m Approx. 70 kg



APLICATOR SYSTEM AB

Metallvägen 3 SE-435 33 Mölnlycke, Sweden Telephone:+46 31 750 30 00 www.aplicatorgroup.com info@aplicator.se Branch offices; Aplicator System ABDenmarkinfo@aplicator.dkFinlandinfo@aplicator.fiSpaininfo@aplicator.esU.Kinfo@aplicator.co.uk