


SCANREX 1K GMM

– One component precision dispensing



1K GMM adapted for robot application



Different nozzles available

The Scanrex 1K GMM is the perfect solution for precise dispensing of high viscosity one component materials such as silicone, epoxy, polyurethane and MS Polymer. The system can be configured to suit a wide range of applications such as CIPG (cured in place gasket),

bonding and sealing where high accuracy and efficiency is required. The Scanrex 1K GMM is designed to be integrated into a larger system and can handle flow rates from 5ml/minute up to 2000ml/minute at continuous flow.

SCANREX 1K GMM

– One component precision dispensing

SERVO-DRIVEN GEAR METERING PUMP

The system is based on a servo-driven gear metering pump where the size of motor and pump enables that the system can be configured for different applications. The servo-driven system ensures highly accurate control over the dispensing.



ADVANCED ALARM HANDLING

Ensure safety and reliability with extensive alarm control, including visual warnings and system stops for critical limits. Torque limitation for motors and pressure sensors for A-and B-component is standard.

VERSATILE DISPENSING SYSTEM

The system offers two different driving modes: continuous flow and shot dispensing.

Continuous flow: Set the flow rate in ml/s. Start and stop the flow using the trigger, foot pedal, an external signal or control station.

Shot dispensing: Set the flow rate and shot size. Dispensing begins with the trigger, foot pedal, or an external signal and stops automatically when the selected shot volume is reached.

The operators can seamlessly switch between the two driving modes as needed.

PUMP SOLUTIONS FOR DIFFERENT MATERIAL CONTAINERS

The material is fed with the SCANREX HVP-series, designed for pumping high viscosity material. The material is pumped directly from the original container, whether it's a 310ml cartridge, 20L bucket or 200L drum.



SCANREX 1K GMM

– One component precision dispensing

STANDARD MACHINE CONFIGURATION

- HVP pump for 20L
- High pressure hoses PA or PTFE
- Material pressure regulator
- Servo-driven metering pump (gear)
- 1K application valve
- Control system with functions such as;
 - Different driving modes with possibility to choose bead diameter and flow (ml/s)
 - Pressure monitoring
 - Low-level monitoring
- FAT (Factory Accept Test) with actual material is always executed before delivery.

OPTIONS

- HVP pump for 310ml cartridge or 200L drum
- Filter for HVP pump
- Mass flow meters
- Heating system
- Different application valves and nozzles
- Double HVP pump setup for automatic material container changeover to ensure seamless production

TECHNICAL DATA

Capacity:	up to 2000ml/minute
Motors:	Servo 400W / 750W
Gear pumps:	From 0,05 cc/rev to 50 cc/rev (standard from 0,3 - 12 cc/rev)
Pneumatic supply:	6-7 Bar
Air consumption:	Depending on feed unit
Electricity supply (stand. config.):	230 VAC 50Hz, 16A

All data and characteristics mentioned in this booklet are by way of example only. Given flow capacities and material pressure are depending of; inlet air pressure, material viscosity, the hose dimensions and other equipment fitted after the pump outlet. Aplicator Group reserves the right to modify the products without prior notice.